



Link-Belt™ Large-Bore Spherical Roller Bearings

SAF/SDAF INTERCHANGE



SAF/SDAF INTERCHANGE

BORE		COMPLETE ASSEMBLY		BEARING		
Inch	Metric	Link-Belt Part Number	Industry Standard Part Number	Link-Belt Part Number	SKF Part Number	FAG Part Number
	220	PLB22244	SAF22244	22244LBC3	22244CC-C3-W33	22244-BE-XL-C3
7-15/16		PLB22544K71516	SAF22544	22244LBKC3	22244CC-K-C3-W33	22244-BE-XL-K-C3
8		PLB22544K8	SAF22544 x 8	22244LBKC3	22244CC-K-C3-W33	22244-BE-XL-K-C3
7-15/16		PLB23044K71516	SAF23044KA x 7 15/16	23044LBKC3	23044-CC-K-C3-W33	23044-BE-XL-K-C3
8		PLB23044K8	SAF23044KA x 8	23044LBKC3	23044-CC-K-C3-W33	23044-BE-XL-K-C3
8-1/2		PLB23048K812	SAF23048KA x 8 1/2	23048LBKC3	23048-CC-K-C3-W33	23048-BE-XL-K-C3
8-15/16		PLB23048K81516	SAF23048KA x 8 15/16	23048LBKC3	23048-CC-K-C3-W33	23048-BE-XL-K-C3
9		PLB23048K9	SAF23048KA x 9	23048LBKC3	23048-CC-K-C3-W33	23048-BE-XL-K-C3
	240	PLB23248	SDAF23248	23248LBC3	23248-CC-C3-W33	23248-BE-XL-C3
8-15/16		PLB23248K81516	SDAF23248KA x 8 15/16	23248LBKC3	23248-CC-K-C3-W33	23248-BE-XL-K-C3
9-7/16		PLB23052K9716	SAF23052KA x 9 7/16	23052LBKC3	23052-CC-K-C3-W33	23052-BE-XL-K-C3
9-7/16		PLB23152K9716	SDAF23152KA x 9 7/16	23152LBKC3	23152-CAC-K-C3-W33	23152-BE-XL-K-C3
	260	PLB23152	SDAF23152	23152LBC3	23152-CAC-C3-W33	23152-BE-XL-K-C3
	260	PLB23252	SDAF23252	23252LBC3	23252-CAC-C3-W33	23252-BEA-XL-MB1-C3
9-7/16		PLB23252K9716	SDAF23252 KA x 9 7/16	23252LBKC3	23252-CAC-K-C3-W33	23252-BEA-XL-K-MB1-C3
9-1/2		PLB23052K912	SAF23052 KA x 9 1/2	23052LBKC3	23052-CC-K-C3-W33	23052-BE-XL-K-C3
9-15/16		PLB23056K91516	SAF23056 KA x 9 15/16	23056LBKC3	23056-CAC-K-C3-W33	23056-BE-XL-K-C3
10		PLB23056K10	SAF23056 KA x 10	23056LBKC3	23056-CAC-K-C3-W33	23056-BE-XL-K-C3
10-7/16		PLB23056K10716	SAF23056KA x 10 7/16	23056LBKC3	23056-CAC-K-C3-W33	23056-BE-XL-K-C3
	280	PLB23156	SDAF23156	23156LBC3	23156-CAC-C3-W33	23156-BE-XL-C3
10-7/16		PLB23156K10716	SDAF23156KA x 10 7/16	23156LBKC3	23156-CAC-K-C3-W33	23156-BE-XL-K-C3
	280	PLB23256	SDAF23256	23256LBC3	23256-CAC-C3-W33	23256-BEA-XL-MB1-C3
10-7/16		PLB23256K10716	SDAF23256KA x 10 7/16	23256LBKC3	23256-CAC-K-C3-W33	23256-BEA-XL-K-MB1-C3
	300	PLB23060	SDAF23060	23060LBC3	23060-CAC-C3-W33	23060-BE-XL-C3
10-15/16		PLB23060K101516	SDAF23060KA x 10 15/16	23060LBKC3	23060-CAC-K-C3-W33	23060-BE-XL-K-C3
	300	PLB23160	SDAF23160	23160LBC3	23160-CAC-C3-W33	23160-BEA-XL-K-MB1-C3
10-15/16		PLB23160K101516	SDAF23160KA x 10 15/16	23160LBKC3	23160-CAC-K-C3-W33	23160-BEA-XL-MB1-C3
	300	PLB23260	SDAF23260	23260LBC3	23260-CAC-C3-W33	23260-BEA-XL-MB1-C3
10-15/16		PLB23260K101516	SDAF23260KA x 10 15/16	23260LBKC3	23260-CAC-K-C3-W33	23260-BEA-XL-K-MB1-C3
11		PLB23060K11	SDAF23060KA x 11	23060LBKC3	23060-CAC-K-C3-W33	23060-BE-XL-K-C3
	320	PLB23064	SDAF23064	23064LBC3	23064-CC-C3-W33	23064-BEA-XL-MB1-C3
11-15/16		PLB23064K111516	SDAF23064KA x 11 15/16	23064LBKC3	23064-CC-K-C3-W33	23064-BEA-XL-K-MB1-C3
	320	PLB23164	SDAF23164	23164LBC3	23164-CAC-C3-W33	23164-BEA-XL-MB1-C3
11-15/16		PLB23164K111516	SDAF23164KA x 11 15/16	23164LBKC3	23164-CAC-K-C3-W33	23164-BEA-XL-K-MB1-C3
11-15/16		PLB23264K111516	SDAF23264KA x 11 15/16	23264LBKC3	23264-CAC-K-C3-W33	23264-BEA-XL-K-MB1-C3
	320	PLB23264	SDAF23264	23264LBC3	23264-CC-C3-W33	23264-BEA-XL-MB1-C3
12		PLB23064K12	SDAF23064KA x 12	23064LBKC3	23064-CC-K-C3-W33	23064-BEA-XL-K-MB1-C3
12-1/2		PLB23068K1212	SDAF23068KA x 12 1/2	23068LBKC3	23068-CAC-K-C3-W33	23068-BEA-XL-K-MB1-C3
	340	PLB23068	SDAF23068	23068LBC3	23068-CAC-C3-W33	23068-BEA-XL-MB1-C3
	340	PLB23168	SDAF23168	23168LBC3	23168-CAC-C3-W33	23168-BEA-XL-MB1-C3
12-7/16		PLB23168K12716	SDAF23168KA x 12 7/16	23168LBKC3	23168-CAC-K-C3-W33	23168-BEA-XL-K-MB1-C3
	340	PLB23268	SDAF23268	23268LBC3	23268-CA-C3-W33	23268-BEA-XL-MB1-C3

SAF/SDAF INTERCHANGE

BORE		COMPLETE ASSEMBLY		BEARING		
Inch	Metric	Link-Belt Part Number	Industry Standard Part Number	Link-Belt Part Number	SKF Part Number	FAG Part Number
12-7/16		PLB23268K12716	SDAF23268KA x 12 7/16	23268LBKC3	23268-CA-K-C3-W33	23268-BEA-XL-K-MB1-C3
12-15/16		PLB23072K121516	SDAF23072KA x 12 15/16	23072LBKC3	23072-CAC-K-C3-W33	23072-BEA-XL-K-MB1-C3
13		PLB23072K13	SDAF23072KA x 13	23072LBKC3	23072-CAC-K-C3-W33	23072-BEA-XL-K-MB1-C3
13-7/16		PLB23172K13716	SDAF23172KA x 13 7/16	23172LBKC3	23172-CAC-K-C3-W33	23172-BEA-XL-K-MB1-C3
	360	PLB23172	SDAF23172	23172LBC3	23172-CAC-C3-W33	23172-BEA-XL-MB1-C3
	360	PLB23272	SDAF23272	23272LBC3	23272-CA-C3-W33	23272-BEA-XL-MB1-C3
13-7/16		PLB23272K13716	SDAF23272KA x 13 7/16	23272LBKC3	23272-CA-K-C3-W33	23272-BEA-XL-K-MB1-C3
13-15/16		PLB23076K131516	SDAF23076KA x 13 15/16	23076LBKC3	23076-CAC-K-C3-W33	23076-BEA-XL-K-MB1-C3
	380	PLB23176	SDAF23176	23176LBC3	23176-CA-C3-W33	23176-BEA-XL-MB1-C3
13-15/16		PLB23176K131516	SDAF23176KA x 13 15/16	23176LBKC3	23176-CA-K-C3-W33	23176-BEA-XL-K-MB1-C3
	380	PLB23276	SDAF23276	23276LBC3	23276-CA-C3-W33	23276-BEA-XL-MB1-C3
13-15/16		PLB23276K131516	SDAF23276KA x 13 15/16	23276LBKC3	23276-CA-K-C3-W33	23276-BEA-XL-K-MB1-C3
14		PLB23076K14	SDAF23076KA x 14	23076LBC3	23076-CAC-C3-W33	23076-BEA-XL-MB1-C3
15		PLB23080K15	SDAF23080KA x 15	23080LBKC3	23080-CAC-K-C3-W33	23080-BEA-XL-K-MB1-C3
	400	PLB23180	SDAF23180	23180LBC3	23180-CA-C3-W33	23180-BEA-XL-MB1-C3
15		PLB23180K15	SDAF23180KA x 15	23180LBKC3	23180-CA-K-C3-W33	23180-BEA-XL-K-MB1-C3
	400	PLB23280	SDAF23280	23280LBC3	23280-CA-C3-W33	23280-BEA-XL-MB1-C3
15		PLB23280K15	SDAF23280KA x 15	23280LBKC3	23280-CA-K-C3-W33	23280-BEA-XL-K-MB1-C3
15-3/4		PLB23084K1534	SDAF23084KA x 15 3/4	23084LBKC3	23084-CA-K-C3-W33	23084-BEA-XL-K-MB1-C3
	420	PLB23184	SDAF23184	23184LBC3	23184-C-J-C3-W33	23184-BEA-XL-MB1-C3
15-3/4		PLB23184K1534	SDAF23184KA x 15 3/4	23184LBKC3	23184-C-K-J-C3-W33	23184-BEA-XL-K-MB1-C3
	420	PLB23284	SDAF23284	23284LBC3	23284-CA-C3-W33	23284-BEA-XL-MB1-C3
15-3/4		PLB23284K1534	SDAF23284KA x 15 3/4	23284LBKC3	23284-CA-K-C3-W33	23284-BEA-XL-K-MB1-C3
16-1/2		PLB23088K1612	SDAF23088KA x 16 1/2	23088LBKC3	23088-CA-K-C3-W33	23088-BEA-XL-K-MB1-C3
	440	PLB23188	SDAF23188	23188LBC3	23188-CA-C3-W33	23188-BEA-XL-MB1-C3
16-1/2		PLB23188K1612	SDAF23188KA x 16 1/2	23188LBKC3	23188-CA-K-C3-W33	23188-BEA-XL-K-MB1-C3
	440	PLB23288	SDAF23288	23288LBC3	23288-CA-C3-W33	23288-BEA-XL-MB1-C3
16-1/2		PLB23288K1612	SDAF23288KA x 16 1/2	23288LBKC3	23288-CA-K-C3-W33	23288-BEA-XL-K-MB1-C3
17		PLB23092K17	SDAF23092KA x 17	23092LBKC3	23092-CA-K-C3-W33	23092-BEA-XL-K-MB1-C3
	460	PLB23192	SDAF23192	23192LBC3	23192-CA-C3-W33	23192-BEA-XL-MB1-C3
17		PLB23192K17	SDAF23192KA x 17	23192LBKC3	23192-CA-K-C3-W33	23192-BEA-XL-K-MB1-C3
18		PLB23096K18	SDAF23096KA x 18	23096LBKC3	23096-CA-K-C3-W33	23096-BEA-XL-K-MB1-C3
	480	PLB23196	SDAF23196	23196LBC3	23196-CA-C3-W33	23196-BEA-XL-MB1-C3
18		PLB23196K18	SDAF23196KA x 18	23196LBKC3	23196-CA-K-C3-W33	23196-BEA-XL-K-MB1-C3
	530	PLB230530	SDAF230530	230530LBC3	230530-CA-C3-W33	230530-BEA-XL-MB1-C3
19-1/2		PLB230530K1912	SDAF230530KA x 19 1/2	230530LBKC3	230530-CA-K-C3-W33	230530-BEA-XL-K-MB1-C3



LINK-BELT™

Regal Rexnord

Contact us: [regalrexnord.com/contact](https://www.regalrexnord.com/contact)
[regalrexnord.com](https://www.regalrexnord.com)

The proper selection and application of products and components, including assuring that the product is safe for its intended use, are the responsibility of the customer. To view our Application Considerations, please visit <https://www.regalrexnord.com/Application-Considerations>.

To view our Standard Terms and Conditions of Sale, please visit <https://www.regalrexnord.com/Terms-and-Conditions-of-Sale> (which may redirect to other website locations based on product family).

“Regal Rexnord” is not indicative of legal entity. Refer to product purchase documentation for the applicable legal entity. Regal Rexnord and Link-Belt are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
© 2023, 2025 Regal Rexnord Corporation, All Rights Reserved. MCB-BR1-015-LB-EN-US 07/25

